



**elesa**  
Original design EBP. / EBP-B



- 3 Type**
- A** Mounting from the back (threaded blind bore)
  - B** Mounting from the operator's side

Distance bushing GN 628.2

| <b>1</b> $l_1$ | <b>2</b> $d_1$<br>Type A | <b>2</b> $d_2$<br>Type B | <b>2</b> $d_3$ | $d_4$ | $d_5$ | $h_1$ | $h_2$ | $h_3$ | $l_2$ | $l_3$<br>min. | $s$ | A/F | $t_1$ | $t_2$ |
|----------------|--------------------------|--------------------------|----------------|-------|-------|-------|-------|-------|-------|---------------|-----|-----|-------|-------|
| 94 -1          | M 5                      | -                        | 22             | 22,5  | 6,5   | 35    | -     | 18    | 116   | 72            | 7,5 | -   | 10    | -     |
| 94 -1          | M 6                      | 6,5                      | 22             | 22,5  | 6,5   | 35    | 17    | 18    | 116   | 72            | 7,5 | 10  | 12    | 6,5   |
| 117 ±0,5       | M 6                      | 6,5                      | 26             | 26,5  | 8,5   | 39    | 7     | 19,5  | 143   | 91            | 8,5 | 10  | 12    | 19,5  |
| 117 ±0,5       | M 8                      | 8,5                      | 26             | 26,5  | 8,5   | 39    | 18    | 19,5  | 143   | 91            | 8,5 | 13  | 13    | 8,5   |
| 120 ±0,5       | M 6                      | 6,5                      | 27             | 26,5  | 8,5   | 40,5  | 17,5  | 19,5  | 147   | 93            | 9,5 | 10  | 12    | 10,5  |
| 120 ±0,5       | M 8                      | 8,5                      | 27             | 26,5  | 8,5   | 40,5  | 17,5  | 19,5  | 147   | 93            | 9,5 | 13  | 13    | 10,5  |
| 132 ±0,5       | M 6                      | -                        | 27             | -     | -     | 42    | -     | -     | 159   | 105           | 9,5 | -   | 13    | -     |
| 132 ±0,5       | M 8                      | 8,5                      | 27             | 26,5  | 8,5   | 42    | 17,5  | 19,5  | 159   | 105           | 9,5 | 13  | 13    | 10,5  |
| 150 ±1         | M 8                      | 8,5                      | 28             | 29    | 9     | 45    | 18    | 20,5  | 180   | 122           | 9,5 | 13  | 13    | 14    |
| 179 ±1         | M 8                      | 8,5                      | 29             | 29    | 9     | 51    | 19    | 20,5  | 208   | 150           | 9,5 | 13  | 13    | 16    |
| 179 ±1         | M 10                     | -                        | 29             | -     | -     | 51    | -     | -     | 208   | 150           | 9,5 | -   | 13    | -     |

**Specification**

**Handle**

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black-gray, matte, similar RAL 7021

**Threaded bushings** for type A  
Brass

**Cover caps**

- Plastic, Polyamide (PA)
- Black-gray, RAL 7021, matte finish
- Orange, RAL 2004, matte finish
- Gray, RAL 7035, matte finish
- Yellow, RAL 1021, matte finish
- Blue, RAL 5024, matte finish
- Red, RAL 3000, matte finish
- Green, RAL 6017, matte finish

- **DSG**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

RoHS

**Technical Information**

|                           |     |
|---------------------------|-----|
| Product Family Ergostyle® | QVX |
| Strength Properties       | QVX |
| Plastic Characteristics   | QVX |

Cabinet U-handles GN 628 are designed with ergonomic shapes to match the Ergostyle product family. They can also be used as complementary handles for cabinet U-handles GN 628.4 and GN 628.5 with electrical and pneumatic switching function.

The cover caps for type A are supplied ready assembled, for type B they are enclosed loose.

The distance to the screw-on surface can be extended with distance bushings GN 628.2.

see also...

|   | Page |
|---|------|
| <b>GN 628.1</b> Cabinet U-Handles (Antimicrobial Plastic)             | QVX  |
| <b>GN 628.3</b> Cabinet U-Handles (Made of Flexible Plastic)          | QVX  |
| <b>GN 628.4</b> Cabinet U-Handles (with Power Switching Function)     | QVX  |
| <b>GN 628.5</b> Cabinet U-Handles (with Pneumatic Switching Function) | QVX  |

**How to order**

|                             |
|-----------------------------|
| <b>1</b> $l_1$              |
| <b>2</b> $d_1$ ( $d_2$ )    |
| <b>3</b> Type               |
| <b>4</b> Color (Cover caps) |

**GN 628-150-8,5-B-DSG**

**How to order (Distance bushing)**

|                |
|----------------|
| <b>5</b> $h_3$ |
|----------------|

**GN 628.2-20,5**