



1.1

1.2


1.3

1.4

Electrical and mechanical characteristics

Button


Contacts 1x normally open / 1x normally closed
 Switching voltage max. 28 V DC / 30 V AC
 Switching current max. 1 A
 mech. life expectancy 10⁶ operating cycles



2.1

LED

Operating voltage 24 ± 15 % V DC
 Color left - green
 right - red




2.2

2.3

Connection type

Cable (Type KL / KR / KU) PUR-cable with 2,5 m or 5 m length
 or
 Connector (Type SL / SR / SU) Connector M12x1, 8-pole
 Protection class IP65

Pin configuration and cable assignment



- 1 - white
- 2 - brown
- 3 - green
- 4 - yellow
- 5 - gray
- 6 - pink
- 7 - blue
- 8 - red

2.4

