



$d_1$	$d_2$	$d_3$	$d_4$	$l_1 \approx$	$l_2$	$l_3 \approx$
M 10	24	10,5	8	68	30	20
M 12	26	13	9	82	36	24,5
M 16	32	17	10	98	45	32

### Specification

- Steel  
Zinc plated, blue passivated
- Butt-welded toggle
- RoHS

### On request

- In stainless steel

### Information

Quick release toggle nuts GN 6336.3 are used in such applications where the knob has to be completely removed after the releasing operation and refitted rapidly for re-clamping.

Plug the toggle nut onto the threaded bolt at an oblique angle. During the clamping action, it engages into the threads of the bolt.

see also...

- Quick Release Knurled Nuts GN 6303.1 → Page 644
- Quick Release Star Knobs GN 6336.3 → Page 550

How to order

**GN 6305.1-M16-ST**

- |   |          |
|---|----------|
| 1 | $d_1$    |
| 2 | Material |