



d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> min.
M 10	18	8	80	60	20
M 12	20	10	100	70	25
M 16	24	13	120	85	35
M 20	30	16	140	95	40

### Specification

- Steel  
Property class 5  
Blackened
- Bar end caps  
Plastic, gray
- *Strength Values of Nuts* → Page 2152
- RoHS

### Information

The movable bar of the tommy nut DIN 6307 is held in any position by the pressure spring.

The plastic end caps limit the travel distance. They are pressed on with form-lock and may be supplied separately if the parts are to be electroplated. The official DIN standard sheets provides steel rings at this point.

How to order

**DIN 6307-M12**

1 d<sub>1</sub>

