



d₁	d₂		Length l						d₃	b	h₁	h₂
40	M 5	-	16	20	30	-	-	13,5	6	20	4	
40	M 6	M 8	16	20	25	30	40	13,5	6	20	4	
48	M 5	-	16	20	30	-	-	13,5	7	24	5,5	
48	M 6	M 8	16	20	25	30	40	13,5	7	24	5,5	
55	M 8	M 10	20	30	40	-	-	16	8	28	6,5	
63	M 8	M 10	20	30	40	-	-	19	9	32	7,5	
70	M 8	-	20	30	40	-	-	20	10	36	8	
70	M 10	-	20	30	40	-	-	20	10	36	8	

Specification

- Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 130 °C
 - Black-gray, similar to RAL 7021, matte

- Threaded stud
Steel
Zinc plated, blue passivated

- Color of the cover cap (matte finish):
 - Black-gray, RAL 7021
 - Orange, RAL 2004
 - Gray, RAL 7035
 - Yellow, RAL 1021
 - Blue, RAL 5024
 - Red, RAL 3000
 - Green, RAL 6017



- Plastic Characteristics → Page 2158

- RoHS



Information

Design and handling of the wing screws GN 633 comply with the requirements and claims of the product family Ergostyle®.

see also...

- Product Family Ergostyle® → Page 18
- Wing Screws GN 639 (Small Type) → Page 613
- Wing Nuts GN 634 → Page 606
- Stainless Steel Wing Screws GN 835 → Page 619
- Wing Screws GN 633 / GN 633.1 with Loss Protection GN 111.7 → Page 2084

How to order

1	d₁
2	d₂
3	Length l
4	Color of the cover cap

GN 633-55-M8-30-DGR