



d ₁	d ₂	Length l ≈										d ₃	h ₁	h ₂	
		GN 6336.4					GN 6336.5								
32	M 6	16	20	25	30	35	45	-	-	-	-	-	12	20	9
40	M 8	16	20	25	30	40	55	20	25	30	40	-	14	25	12
50	M 10	25	30	35	45	55	-	20	25	30	45	55	18	32	15
63	M 12	30	35	40	50	60	-	30	40	50	-	-	20	40	19
80	M 16	30	40	50	60	70	-	-	-	-	-	-	25	50	23

Specification

GN 6336.4

Knob
Cast iron **SG**
Fettled and tumbled
Threaded stud
Steel
screwed in and secured by a cross-dowel

see also...

	Page
GN 6336.4 Star Knobs (Plastic, Threaded Stud Steel)	QVX / QVX
GN 6336.5 Star Knobs (Plastic, Threaded Stud Stainless Steel)	QVX / QVX
GN 5334 GN 5334.4 Star Knobs with Threaded Stud (Stainless Steel)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

GN 6336.5

Knob
• Stainless steel precision casting AISI CF-8 **ES**
Matte shot-blasted
• Cast iron, forged **AM**
- Tumbled **AP**
- Polished

Threaded stud

Stainless steel
Screwed in and secured by a cross-dowel

RoHS

How to order (Threaded stud steel)

GN 6336.4-SG-63-M12-50

- 1 Material
- 2 d₁
- 3 d₂
- 4 Length l

How to order (Threaded stud stainless steel)

GN 6336.5-AM-40-M8-25

- 1 Finish
- 2 d₁
- 3 d₂
- 4 Length l

