



Inox
Stainless
Steel

1		2															
d ₁	l ₁ ±1						a	b	d ₂	h ₁	h ₂	l ₂	l ₃	t			
30	300	350	400	500	600	700	1000	57	38	M 10	60	78	23	12	17		

Specification

Handle tube

Wall thickness 1,5 mm

- Aluminum
- Stainless steel
 - Powder coated
 - Black, RAL 9005, textured finish
 - Anodized, natural color
- Stainless steel AISI 304
 - ground, matte shiny

- SW
- EL
- NG

End pieces

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature up to 100 °C
- Black, matte finish
- Threaded bushing brass

RoHS

The handle tube of the cabinet U-handles GN 667.2 can be mounted without any further machining, allowing special length to be realised easily.

see also...

	Page
GN 667 Cabinet U-Handles (Mounting from the Operator's Side)	QVX

Technical Information

Load Rating Information	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 667.2-30-1000-NG

1	d ₁
2	l ₁
3	Finish