



4 Type
A Front rounded

b h9	h	Length l														for shaft-Ø from to
		6	8	10	12	14	16	18	20	-	-	-	-	-	-	
3	3	6	8	10	12	14	16	18	20	-	-	-	-	-	-	8...10
4	4	10	12	14	16	18	20	22	25	28	32	-	-	-	-	10...12
5	5	10	12	14	16	18	20	22	25	28	32	36	40	45	50	12...17
6	6	14	16	18	20	22	25	28	32	36	40	45	50	56	63	17...22
8	7	16	18	20	22	24	25	28	32	36	40	45	50	56	63	22...30
10	8	20	22	25	28	32	36	40	45	50	56	63	70	80	90	30...38
12	8	25	28	32	36	40	45	50	56	63	70	80	90	100	-	38...44

Specification 5
Stainless steel AISI 316Ti NI
 RoHS
On request
 • b = 14, 16, 18, 20

Parallel keys DIN 6885 are only in packing units of 10 pieces for each size and length available.

see also... Page
DIN 6885 Parallel Keys (Steel) QVX

Technical Information	
Keyways DIN 6885-1 (High Hub Keyway)	QVX
Keyways DIN 6885-2 (Low Hub Keyway)	QVX
ISO Fundamental Tolerances	QVX
Stainless Steel Characteristics	QVX

How to order	
1	b
2	h
3	Length l
4	Type
5	Material

1 2 3 4 5
DIN 6885-10-8-36-A-NI