



**3 Type**

- A** Flat pressure area
- B** Rounded pressure area

**1**

**2**

$d_1$	Length l			$d_2$	$d_3$	h	m	r
M 4	23	30	-	8	9,8	5	2,2	6
M 4	33	43	-	8	8	10	2,2	6
M 5	45	55	-	10	9	11	2,7	8
M 6	35	55	65	13	12	12	3,2	10
M 8	43	68	-	16	14	18	4	12
M 10	50	77	97	20	18	21	5	15
M 12	100	130	-	25	23	24	6	18

**Specification**

- Screw
  - Steel **ST**
  - Zinc plated, blue passivated
  - Stainless steel AISI 304 **NI**
- Hexagon nuts ISO 4035
  - Steel
  - Zinc plated, blue passivated
  - Stainless steel AISI 304
- Thrust pad
  - Rubber, Neoprene (CR)
  - 85 Shore A  $\approx$
  - Vulcanized
  - Black
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

**4**

**Information**

The two hexagon nuts are included parts of the order.  
 see also...  
 • *Holders for Clamping Screws GN 801*  
 (for Toggle Clamps with Forked Clamping Arm) → Page 815

**How to order**

<b>1</b>	$d_1$
<b>2</b>	Length l
<b>3</b>	Type
<b>4</b>	Material

**GN 708.1-M5-45-A-NI**