



d ₁	d ₂ h9	d ₃ H7	d ₄	d ₅ +0,1	e	h min.	Length l -0,2	t	for side thrust pin-Ø
6	12	12	M 4	6,2	2	10	9,9	4,4	3
10	16	16	M 4	10,2	2	12	11,9	5,4	5 6
12	18	18	M 4	12,2	2	14	13,9	6,6	8
16	25	25	M 6	16,2	3	18	17,9	7,9	10

Specification

- Steel
Blackened
- Grub screw
Stainless steel
- *ISO Fundamental Tolerances* → Page 2151
- RoHS

Information

Eccentric bushings GN 715.2 allow side thrust pins GN 715 / GN 714 to be adjusted. These bushings allow the side thrust pin to be precisely adjusted to suit the requirements for clamping of a component.

see also...

- *Side Thrust Pins GN 715 (Press-On Type)* → Page 1002
- *Side Thrust Pins GN 714 (without Pressure Pin, Press-On Type)*
→ Page 1003

How to order

GN715.2-6

1 d₁