


**elesa**  
Original design ADT

**Assembly examples**



d <sub>1</sub>	Nominal dimension		a	b	d <sub>2</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub>	s	for cabinet U-handles
	min.	max.										
30	28,6	32	14	23	5	1,5	11	45	5,5	1,5	1,5	GN 725.1-86
30	28,6	32	16	25	6	1,5	13	51	6,5	1,5	1,5	GN 725.1-117

**Specification**

**Plastic, Polyamide (PA)**

- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

RoHS

Adapters GN 725.2 allow you to install GN 725.1 cabinet U-handles on pipes / rods with diameters ranging from 28.6 mm to 32 mm.

**see also...** **Page**  
**GN 725.1 Cabinet U-Handles (Polypropylene)** QVX

**Technical Information**

Plastic Characteristics QVX

**How to order**

**GN 725.2-30-14-23**

1	d <sub>1</sub>
2	a
3	b

