



d ₁	d ₂	l ₁	l ₂	s
G 1/4	20	9	3	6
G 3/8	22	9	4	8
G 1/2	28	11	4	10
G 3/4	32	12	4,5	12

Specification

- Plastic (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Seal
 - Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

Information

see also...

- *Plugs GN 749 (Steel)* → Page 1592

How to order

GN 746-G¹3/8

1 d₁