


Application example



a	h <sub>1</sub>	b <sub>1</sub>	b <sub>2</sub>	d <sub>1</sub>	d <sub>2</sub>	h <sub>2</sub>	m	Length l	for toggle clamps	
									GN 810 GN 810.1 GN 810.3 GN 810.4	GN 820 GN 820.1 GN 820.3 GN 820.4
67,5	16	10	21,5	6,3	M 5	21,5	20	121	130	130
71,5	18	12	26,5	8,2	M 6	24,5	26	142	230	230

Specification

- Steel  
Zinc plated, blue passivated
- RoHS

ST

Information

With clamping arm extenders GN 809.1, various toggle clamps with “solid clamping arm” can be easily and quickly extended. The slot of the extender corresponds to the dimensions of the respective toggle clamp size with “forked clamping arm” and is therefore compatible with all accessories, such as flanged washers, clamping screws, etc.

For assembly, the clamping arm extenders are solid onto the clamping arms of the toggle clamps and bolted into place. The required holes in the clamping arm of the toggle clamp must be made by the user.

All parts are supplied in a non-assembled set. Two flanged washers are included for fastening the clamping screw.

see also...

- Clamping Arm Extenders GN 801.1 (Rigid) → Page 816
- Clamping Arm Extenders GN 801.2 (with Joint) → Page 817
- Clamping Screws GN 804 → Page 810
- Clamping Screws GN 807 → Page 811

How to order

GN809.1-71,5-18-ST

1	a
2	h <sub>1</sub>
3	Material

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

