



elesa
Original design BAS3



Inox
Stainless
Steel



d Bore	For tube outside Ø	Standard description in inch
B 42,4	42,4	1 1/4"
B 48,3	48,3	1 1/2"
B 60,3	60,3	2"

Specification

- Plastic (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Hexagon screws DIN 931
Stainless steel AISI 304
- Hexagon nuts DIN 934
Stainless steel AISI 304
- Washers
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Version with square 45 x 45

Information

see also...

- *Base Plate Connector Clamps GN 83 (Plastic)* → Page 1812
- *Leveling Feet* → Page 1424 ff.
- *Construction Tubes GN 990* → Page 1835

How to order

GN 82-B60,3

1 d