



1 2

d ₁	l ₁ Nominal length										d ₂	d ₃	l ₂	l ₃ ±0,3	A/F ₁	A/F ₂
M 3	3	4	5	6	8	10	-	-	-	-	1,9	1,5	0,5	0,8	1,5	1,5
M 4	4	5	6	-	-	-	-	-	-	-	2,5	2	0,5	1	2	1,5
M 4	8	10	12	16	20	-	-	-	-	-	2,5	2	0,5	1	2	2
M 5	5	6	-	-	-	-	-	-	-	-	3	3	0,5	1	2,5	2
M 5	8	10	12	16	20	25	-	-	-	-	3	3	0,5	1	2,5	2,5
M 6	6	8	10	12	16	20	25	32	40	50	4	3,5	1	1,3	3	3
M 8	8	10	12	16	20	25	32	40	50	63	6	5	1,5	1,6	4	4
M 10	16	20	25	32	40	50	63	80	-	-	8	6,5	2	1,9	5	5
M 12	20	25	32	40	50	63	80	100	-	-	10	8	2	2,1	6	6

Specification

- Screw
Stainless steel AISI 303
- Thrust pivot
 - Brass **MS**
 - Plastic (Polyacetal POM) **KU**
- Plastic Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

3

Information

Stainless steel grub screws GN 913.5 with pivots in brass or plastic are used in applications, where marks and damage on the workpiece are unacceptable.

see also...

- Stainless Steel Ball Point Screws GN 605 (with Flat Ball) → Page 1053

How to order

GN913.5-M6-20-KU

1	d ₁
2	l ₁
3	Material (Thrust pivot)

