



ROSTFREI
Inox
Stainless
Steel

1 d ₁	2 b	3 l ₁	d ₂	l ₃						
					Size	r at w ₂ =0	w ₂	Size	r at w ₂ =0	w ₂
M 10	46	129*	9	45	GN 852 / GN 852.3			GN 852.1		
M 10	46	149**	9	52	1700	96	15	1400	95	15
M 10	46	179	9	45	1700	106	22	1400	109	22
M 10	46	209	9	45	1700	146	15	1400	145	15
M 10	46	259	9	45	1700	176	15	1400	175	15
M 10	46	259	9	45	1700	226	15	1400	225	15
M 12	55	151*	10,8	70	4000	107	25	-	-	-
M 12	55	211	10,8	70	4000	156	36	-	-	-
M 12	55	361	10,8	70	4000	306	36	-	-	-
M 12	55	421	10,8	70	4000	366	36	-	-	-

* These square U-bolt lengths are included in the delivery of standard orders for GN 852 / GN 852.3.

** These square U-bolt length is included in the delivery of standard orders for GN 852.1 and is only available in steel.

Specification

- Steel **ST**
- Zinc plated, blue passivated
- Stainless steel AISI 304 **NI**
- Hex nuts (with polyamide insert)
DIN 936 / DIN 985
 - Steel, zinc plated (for ST)
 - Stainless steel (for NI)
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

- see also...
- *Latch Type Toggle Clamps GN 852* → Page 764 / 766
 - *Latch Type Toggle Clamps GN 852.1* → Page 772
 - *Latch Type Toggle Clamps GN 852.3* → Page 768 / 770

How to order

1	d ₁
2	b
3	l ₁
4	Material

GN 951.2-M10-46-259-ST