


Standard	Characteristics / Features	Materials						Opening angle		Mounting by		Welding
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	the rear	
<b>GN 237</b> Page 959 	very universal, accessory available		x	x	x	x		180°	90°	x	x	
<b>GN 237</b> Page 963 	very universal, extended, accessory available		x		x			180°	90°	x	x	
<b>GN 237.3</b> Page XYZ 			x					180°	90°	x	x	
<b>GN 237.3</b> Page XYZ 			x					180°	90°	x	x	
<b>GN 237.1</b> Page 964 	very universal, accessory available						x	180°	90°	x		
<b>GN 7237</b> New products Page 144 	inside installation, adjustable, accessory available		x					180°	0°	x	x	x*
<b>GN 437.1</b> Page XYZ 	universal				x			180°	90°	x		
<b>GN 136</b> New products Page 148 	Metal sheet, simple square or vertically elongated	x	x					180°	90°	x		x
<b>GN 136</b> New products Page 149 	Metal sheet, simple horizontally elongated	x	x					180°	90°	x		x
<b>GN 1362</b> New products Page 150 	Metal sheet, simple robust		x					180°	90°			x

Standard	Characteristics / Features	Materials						Opening angle		Mounting by		Welding
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	Screw fastening from the rear	
<b>GN 1364</b> New products Page 151 	 <p>Metal sheet, universal elegant, robust</p>		x					180°	90°	x	x	
<b>GN 1366</b> New products Page 152	 <p>Steel profile, simple, very robust</p>	x						180°	100°			x
<b>GN 138</b> Page 966	 <p>elegant design</p>				x			180°	0°		x	
<b>GN 154</b> Page XYZ	 <p>versatile</p>						x	180°	0°	x	x	
<b>GN 155</b> Page XYZ	 <p>versatile</p>						x	120°	70°	x	x	
<b>GN 157</b> Page XYZ	 <p>universal</p>						x	180°	20° resp. 95°	x		
<b>GN 158</b> Page XYZ	 <p>universal</p>						x	180°	90°	x	x	
<b>GN 151</b> Page 965	 <p>versatile</p>						x	180°	40°	x	x	
<b>GN 151.3</b> New products Page 154	 <p>elegant design</p>						x	180°	20°	x		
<b>GN 151.5</b> New products Page 155	 <p>universal</p>						x	180°	20°	x		

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9



Standard	Characteristics / Features	Materials						Opening angle		Mounting by		Welding
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	the rear	
GN 2295 Page XYZ	 for profile systems / panel elements					x		∞	∞	x		
GN 2295 Page XYZ	 for profile systems / panel elements, vertical elongated					x		∞	∞	x		
GN 159 Page 968 	 for profile systems						x	180°	100°	x		
GN 159.1 Page 970	 for profile systems						x	180°	95°	x		
GN 161 Page 972 	 for profile systems						x	180°	90°	x		
GN 129 Page 974	 Corner mounted, two or three parts	x						∞	∞		x	
GN 129.5 Page 975 	 Corner mounted, three parts		x	x				∞	∞		x	
GN 129.2 Page 976 	 extended three parts	x	x	x				180°	90°		x	
GN 129.3 Page 977	 extended three parts	x						180°	90°	x		
GN 235 New products Page 156 	 adjustable, very universal, accessory available		x		x			180°	15°	x	x	

Standard	Characteristics / Features	Materials						Opening angle		Mounting by		
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from		Welding
										the front	the rear	
GN 127 Page 980				x	x			170°	90°	x		
GN 238 Page 978					x			160°	20°	x		
GN 236 Page XYZ							x	180°	90°	x		
GN 151.4 Page 981							x	180°	30°	x		
GN 337 Page 986	 <small>RoHS proof Iron Stainless Steel</small>		x		x			180°	90°	x		
GN 337.1 Page XYZ							x	180°	90°	x		
GN 2292 Page XYZ						x		∞	∞	x		
GN 2294 Page XYZ						x		∞	∞	x		
GN 161.1 Page 988					x		x	∞	∞	x	x	
GN 161.2 Page 989					x			180°	0°		x	

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9



Standard	Characteristics / Features	Materials						Opening angle		Mounting by			
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	Screw fastening from the rear	Welding	
GN 160 Page XYZ	 detachable, with eccentric pin adjustable							x	∞	∞	x	x	
GN 160.1 Page XYZ	 elegant design, detachable, with eccentric pin							x	180°	0°	x		
GN 128 Page 990	 Corner mounted, detachable	x							∞	∞			x
GN 128.2 Page 991 	 Corner mounted, detachable		x	x		x			∞	∞			x
GN 437 Page 982	 with adjustable friction, accessory available				x				180°	90°	x		
GN 233 Page 984	 with adjustable friction							x	180°	90°	x		
GN 437.2 Page XYZ	 with clamp				x				180°	90°	x		
GN 151.2 Page XYZ	 lockable							x	180°	40°	x		
GN 437.4 Page XYZ	 with detent				x				180°	90°	x		
GN 222 Page XYZ	 with 4 indexing positions							x	115°	90°	x		

Standard	Characteristics / Features	Materials						Opening angle		Mounting by			
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	Screw fastening from the rear	Welding	
GN 122.1 Page XYZ	 with 4 indexing positions							x	180°	15°	x		
GN 122.2 Page XYZ	 without indexing positions							x	180°	15°	x		
GN 437.3 Page XYZ	 with spring-loaded return				x				180°	90°	x		
GN 233.3 New products Page 157	 with or without spring-loaded return							x	180°	90°	x		
GN 139.1 Page 992	 with electrical safety switch function				x				180°	0°		x	
GN 139.2 Page 992	 without switch				x				180°	0°		x	
GN 139.5 Page 996 	 with electrical safety switch function			x					180°	0°		x	
GN 139.6 Page 996 	 without switch			x					180°	0°		x	
GN 239.6 Page 998	 with electrical safety switch function							x	180°	0°	x	x	
GN 239.7 Page 998	 without switch							x	180°	0°	x	x	

3.1

3.2

3.3

3.4

3.5



3.6

3.7

3.8

3.9



Standard	Characteristics / Features	Materials						Opening angle		Mounting by		Welding
		ST	NI	A4	ZD	AL	KT	positive	negative	Screw fastening from the front	Screw fastening from the rear	
<b>GN 239.4</b> Page 1002 	with electrical switch function						×	180°	10°	×		
<b>GN 239.3</b> Page 1002 	without switch						×	180°	10°	×		