


Zubehör für Kniehebelmodule


zum Anschweißen, für GN 910.2 und GN 910.3

Griffe



| Modul Größe | b ₁ | b ₂ | b ₃ | d ₁ | d ₂ | h | t | Artikel-Nr. |
|-------------|----------------|----------------|----------------|----------------|----------------|-----|-----|---------------|
| 220 | 22 | 13 | 5 | - | - | 60 | 55 | GN 910.5-220 |
| 440 | 31 | 20 | 8 | - | - | 86 | 77 | GN 910.5-440 |
| 850 | - | - | - | 30 | 22 | 119 | 112 | GN 910.5-850 |
| 1540 | - | - | - | 34 | 25 | 119 | 112 | GN 910.5-1540 |

Hebelarme



| Modul Größe | b | d | Länge l | s | Artikel-Nr. |
|-------------|----|----|---------|---|---------------|
| 220 | 13 | - | 60 | 5 | GN 910.6-220 |
| 440 | 20 | - | 90 | 8 | GN 910.6-440 |
| 850 | - | 22 | 122 | - | GN 910.6-850 |
| 1540 | - | 25 | 138 | - | GN 910.6-1540 |

GN 910.5


GN 910.6

GN 910.7

GN 910.8


GN 910.9

Spannarmverlängerungen




| Modul Größe | b ₁ | b ₂ | h | Länge l | t | Artikel-Nr. |
|-------------|----------------|----------------|----|---------|-----|---------------|
| 220 | 10 | 6 | 16 | 15,5 | 6,5 | GN 910.7-220 |
| 440 | 15 | 10 | 24 | 16 | 8 | GN 910.7-440 |
| 850 | 20 | 12 | 30 | 22,1 | 15 | GN 910.7-850 |
| 1540 | 25 | 16,2 | 35 | 23,5 | 15 | GN 910.7-1540 |

Buchsen



| Modul Größe | d ₁ | d ₂ | Länge l | Artikel-Nr. |
|-------------|----------------|----------------|---------|---------------|
| 220 | 13 | 6,5 | 16 | GN 910.8-220 |
| 440 | 20 | 10,5 | 24 | GN 910.8-440 |
| 850 | 24 | 12,5 | 30 | GN 910.8-850 |
| 1540 | 32 | 16,5 | 35 | GN 910.8-1540 |

Grundplatten



| Modul Größe | d | l ₁ | l ₂ | m ₁ | m ₂ | s | Artikel-Nr. |
|-------------|------|----------------|----------------|----------------|----------------|----|---------------|
| 220 | 6,5 | 48 | 36 | 32 | 20 | 6 | GN 910.9-220 |
| 440 | 8,5 | 65 | 54 | 45 | 30 | 8 | GN 910.9-440 |
| 850 | 10,5 | 75 | 75 | 55 | 55 | 10 | GN 910.9-850 |
| 1540 | 12,5 | 100 | 90 | 65 | 65 | 10 | GN 910.9-1540 |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

