



l_1 max. see standard sheets

Information

For the series with oil dipstick shown above, a shortening and / or the attachment of level markings can be ordered with the service GN 109.

The dipstick is shortened to the length l_1 and the marking notches are milled at l_2 or l_3 , making them easily visible. The **max. length l_1** is specified in the respective series. The length specifications l_1 to l_3 refer to the contact surface without seal, with a tolerance of ± 1 mm to be taken into account. For critical applications, the seal must be taken into consideration with a thickness of up to 2 mm, depending on the series.

If required, more than 2 notches may be inserted on request, which are then specified by appropriate details on the position ($l_4 \dots l_n$). Furthermore, texts such as MAX / MIN may be laser-engraved in addition to or instead of the notches by submitting the appropriate template.

<p>How to order (With special length)</p> <p>GN 109-85</p>	<p>1 l_1 (Length oil dipstick)</p>	<p>Oil filler plug GN 748-30-20-B-1 with oil dipstick in special length GN 109-85</p>
<p>How to order (With one marking notch)</p> <p>GN 109-110-90</p>	<p>1 l_1 (Length oil dipstick)</p> <p>2 l_2 (Dimension notch)</p>	<p>Breather cap GN 552-42-G3/4-B-1 with one level marking GN 109-110-90</p>
<p>How to order (With two marking notches)</p> <p>GN 109-90-80-50</p>	<p>1 l_1 (Length oil dipstick)</p> <p>2 l_2 (Dimension 1st notch)</p> <p>3 l_3 (Dimension 2nd notch)</p>	<p>Threaded plug GN 747-G1-B-2 with two level markings GN 109-90-80-50</p>

