




1						2		b ₂	b ₃	d ₁	d ₂	h ₁	h ₂	l ₂	l ₃	s
25						250		34	22	5,3	22,5	11,7	8	8	17	1,5
400						600										
1000						1500										

Specification	
Fasteners	
Stainless steel AISI 304	NI
Strap	
Plastic, polyester	
• Woven	
• Black	
RoHS	
Technical Information	
Application Examples	
Plastic Characteristics	2158
Stainless Steel Characteristics	2166

Retaining straps GN 1112 have a fixed length. When used as a holding strap, they limit the opening angle of doors and covers or serve as bracing or gripping elements. Thanks to the fasteners permanently sewn onto the ends, the retaining straps can be securely screwed or riveted in place.

Types AD and BD can be quickly and easily attached or detached thanks to the additional hook latch. Type BF can be compactly secured to the body of a latch by means of an external thread (e.g. GN 115) so that they require no further fastening.

Retaining straps GN 1112 may not be used for lifting loads or for lashing.

How to order	
1	b ₁
2	l ₁
3	Type
4	Material
5	Color

GN 1112-25-600-BB-NI-B