




1	2		b ₂	b ₃	d	h ₁	h ₂	l ₂	s
	b ₁	l ₁ ≈ min. max.							
	25	250 410	34	22	5,3	11,7	8	8	1,5
	25	400 710	34	22	5,3	11,7	8	8	1,5
	25	600 1110	34	22	5,3	11,7	8	8	1,5

Specification

Fasteners

Stainless steel AISI 304

NI

Strap

Plastic, polyester

• Woven

• Black

● B

RoHS	
Technical Information	ganternorm.com
Application Examples	
Plastic Characteristics	2158
Stainless Steel Characteristics	2166

Retaining straps GN 1113 can be adjusted to any length by means of the bar buckle. When used as a holding strap, they limit the opening angle of doors and covers or serve as bracing or a carry strap.

Thanks to the fasteners permanently sewn onto the ends, the retaining straps can be securely screwed or riveted in place. Types AD and BD can be quickly and easily attached or detached thanks to the additional hook latch. Retaining straps GN 1113 may not be used for lifting loads or for lashing.

see also... ganternorm.com

GN 1110 Tension Straps (Single-Part)

GN 1111 Tension Straps (Multi-Part)

GN 1112 Retaining Straps (Fixed Length)

How to order

1

2

3

4

5

GN 1113-25-600-BB-NI-B

1	b ₁
2	l ₁
3	Type
4	Material
5	Color