


**1** Type

- DK** With triangular spindle
- VK7** With square spindle
- VK8** With square spindle
- SCH** With slot
- VDE** With double bit
- SK10** With hexagon



**2**

| Latch arm distance A |    |    |    |    |    |    |    |    |    |    |  | d  | h |
|----------------------|----|----|----|----|----|----|----|----|----|----|--|----|---|
| 4                    | 8  | 13 | 16 | 20 | 24 | 28 | 32 | 36 | 40 | 45 |  | 28 | 4 |
| 6                    | 10 | 14 | 18 | 22 | 26 | 30 | 34 | 38 | 42 | 50 |  | 28 | 4 |

**Specification**

- Lock housing  
Zinc die casting
- Housing collar, chrome plated —
- Housing collar  
Powder coated
- Black, RAL 9005, textured finish ● **SW**
- Other parts  
Steel, zinc plated, blue passivated
- Protection class IP65
- IP Protection Classes → Page 2153
- RoHS

**Accessory**

- Socket Keys GN 119.2 → Page 1266
- Protective Caps GN 120 → Page 1268
- Opening Handles GN 120.1 → Page 1269
- Protective Guide Plates GN 120.2  
→ Page 1270
- Internal Cabinet Handles GN 120.3  
→ Page XYZ
- Sheet metal punches GN 123 → Page XYZ

**On request**

- Other operations

**Information**

Latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A from 4 to 50 mm.

Latches GN 115 are supplied with loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → Page 1201
- List of Latch Types → Page 1196 ff.
- Latches GN 115 (with Operating Elements) → Page 1200
- Stainless Steel Latches GN 115 (Operation with Socket Keys)  
→ Page 1207

How to order (Housing collar, chrome plated)

|          |                      |
|----------|----------------------|
| <b>1</b> | Type                 |
| <b>2</b> | Latch arm distance A |

**GN 115-VK8-20**

How to order (Housing collar, black)

|          |                      |
|----------|----------------------|
| <b>1</b> | Type                 |
| <b>2</b> | Latch arm distance A |
| <b>3</b> | Finish               |

**GN 115-SCH-32-SW**