



- 2 Type**
- ST** With fixed steel pin
 - MS** With fixed brass pin
 - STL** With loose steel pin
 - STS** With fixed steel pin and lubricating nipple



Length I	Type ST Type MS	Type STL Type STS	d ₁	d ₂ Pin	s ₁	s ₂
40	-	-	8	5	10	1,8
50	-	-	8	5	10	1,8
60	-	-	10	6	12	1,8
80	80	-	13	8	15,5	2
100	100	-	16	10	20	2,25
120	120	-	16	11	20	2,25
135	135	-	18	12	23	2,5
150	150	-	20	13	25,5	2,5
180	180	-	20	14	25,5	2,5
200	200	-	23	16	28,5	3

Specification

- Steel
Plain
- Pin
 - Steel, plain (Type ST / STS / STL)
 - Brass (Type MS)
- Washer
Brass
- Lubricating nipple DIN 71412-A
Steel, zinc plated
- RoHS

Information

Hinges GN 128 are produced from drawn weldable profiled steel extrusions.

Types ST, STS and MS feature a hinge pin fixed in the lower half of hinge. Type STL with loose steel pin allows the easy installation when attaching several hinges in parallel or if the door is very heavy.

The upper half of Type STS hinge has an additional lubricating nipple DIN 71412-A which allows the hinges to be lubricated without dismantling the hinges.

see also...

- List of Hinge Types → Page 1284 ff.

How to order

GN 128-80-ST

1 Length I

2 Type