



3 Type

- A** 2x2 threaded blind bores for socket cap screws
- B** 2x2 bores for socket cap screws
- C** 2x2 bores for countersunk screws
- D** 2x2 threaded studs
- E** 2x threaded studs 2x bores for socket cap screws
- F** 2x threaded studs 2x bores for countersunk screws
- G** 2x threaded blind bores 2x threaded studs
- H** 2x threaded blind bores 2x bores for socket cap screws
- I** 2x threaded blind bores 2x bores for countersunk screws

1		2		d ₁	d ₂	d ₃	h ₁	h ₂	h ₃	h ₄	l ₃	l ₄	m ₁ ±0,25	m ₂ ±0,25	t ₁	t ₂
l ₁	Nominal size	Actual size	Nominal size	Actual size												
39*	38,5	40	39,5	M 4	4,3	3	14	9	9,5	19	-	14	25	25	6,5	4,5
48	48	49	49,5	M 5	5,5	4	19	11	13	26	14	17	31	30	7	5,5
64	64	65	65	M 6	6,5	5	23	13,5	15	30	18	24	40	40	10	6,5
98	97,5	98	96,5	M 10	10,5	8	35	20,5	23	46	20	35	62,5	59,5	15	10,5

Specification

- Plastic (Polyamide PA)
 - Black, matte finish
 - Temperature resistant up to 80 °C
- Pin
Stainless steel AISI 303
- Threaded bushings brass, nickel plated
- Threaded studs brass, nickel plated
- *Load Rating Information* → Page 2126
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

- see also...
- *List of Hinge Types* → Page 1284 ff.
 - *Hinges GN 151.2 (Lockable)* → Page 1397
 - *Hinges GN 151.4 (Adjustable by Slotted Holes)* → Page 1377

On request

- Plastic (Polyamide) in gray
- Hinges GN 151.1 with opening angle 90°

How to order

GN 151-48-49-B

- 1 l₁
- 2 l₂
- 3 Type

* Only available in type A, B and C.

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9