



2 Type	
<b>MCR</b>	Matte chrome plated
<b>MCRS</b>	Matte chrome plated, standard scale
	0...90, 100 graduations, acc. to scale scheme d <sub>1</sub> /100 A RA 0-10 20...90/10

d <sub>1</sub>	d <sub>2</sub>	d <sub>3</sub> H7	d <sub>4</sub>	l <sub>1</sub>	l <sub>2</sub>	Scaling set consists of 1 scaling ring GN 264	
						2 collar bushings	3 flat springs
30	27	24	33	16	23,7	GN 268-24-K...	GN 374-0,3-10
40	36	32	43	16	23,7	GN 268-32-K...	GN 374-0,4-10
60	55	50	63	16	25,7	GN 268-50-K...	GN 374-0,6-10
80	75	68	83	16	25,7	GN 268-68-K...	GN 374-0,8-10

**Specification**

**Steel**

- Scale lug d<sub>1</sub> fine turned
- Plain finish, without scale
- Matte chrome plated without scale **MCR**
- Matte chrome plated with standard scale **MCRS**
- Scale laser-engraved, black discharged

RoHS

**On request**

- Special graduations (see „How to order - Graduations“)

Scale rings GN 264 can be supplied with any type of scale.

The ordering scheme for scales must be used for the line pattern, number steps, number position and number sequence of any scaling.

**Technical Information**

	Page
How to order - Graduations	QVX
ISO Fundamental Tolerances	QVX

How to order	
1	d <sub>1</sub>
2	Type

**GN 264-40-MCR**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

