


Assembly instruction



d ₁			d ₂	h max.	VE*
	Nominal dimension	Clamping range Ø			
6,1		5,8...6,4	0,9	5	25
6,8		6,6...7	0,9	5	25
7,3		7...7,5	0,9	5	25
7,6		7,3...7,8	0,9	5	25
8,1		7,8...8,3	0,9	5	25
8,6		8,3...8,8	1	5,5	25
9,1		8,8...9,3	1	5,5	25
9,6		9,3...9,9	1	5,5	25
10,1		9,8...10,4	1	5,5	25
10,7		10,4...11	1,2	6,3	25
11,3		11...11,6	1,2	6,3	25
11,9		11,6...12,3	1,2	6,3	25
12,8		12,1...13,1	1,2	6,3	25
13,3		12,9...13,6	1,5	7,3	25
13,7		13,3...14,1	1,5	7,3	25
14		13,6...14,4	1,5	7,3	25
14,8		14,4...15,1	1,5	7,3	25
15,6		14,8...15,9	1,5	7,3	25
15,8		15,5...16,2	1,8	8,4	25
16,4		15,9...16,8	1,8	8,4	25
17,3		16,8...17,7	1,8	8,4	25
18,2		17,7...18,7	1,9	9,1	25
19,2		18,7...19,6	2	9,1	10
20,2		19,6...20,6	2	9,1	10
21,2		20,6...21,6	2	9,1	10

d ₁			d ₂	h max.	VE*
	Nominal dimension	Clamping range Ø			
22,1		21,5...22,6	2	9,1	10
22,6		22...23,1	2,2	10,7	10
23,1		22,5...24	2,2	10,7	10
24,2		23,5...24,7	2,2	10,7	10
25,2		24,4...26	2,2	10,7	10
25,8		25,1...26,4	2,2	10,7	10
26,8		25,8...27,4	2,5	11,4	10
27,5		26,7...28,1	2,5	11,4	10
28,7		27,9...29,4	2,5	11,4	10
30		29,3...30,9	2,5	11,4	10
31,3		30,4...32	2,5	11,4	10
32,7		32...34,1	2,8	12,8	10
34,1		33,2...34,8	2,8	12,8	10
35		33,9...35,7	2,8	12,8	10
35,6		34,6...36,4	3	14	10
37,2		36,2...38	3	14	10
38,8		37,7...39,7	3	14	5
40		38...41	3	14	5
40,5		39,4...41,4	3	14	5
42,9		41...44	3,2	14,8	5
44,4		42,5...45,5	3,2	14,8	5
46		44...47	3,2	14,8	5
47		46...49	3,2	14,8	5
49,8		48,4...50,9	3,2	15,9	5
52		50,6...53,2	3,2	15,9	5

*VE = Packaging units

Specification

Steel

Zinc plated

RoHS

On request

- Additional clamping ranges
- Other materials

2

ST

Spring clamps GN 3017.5 secure hose assemblies to hose barbs and hose nipples in low-pressure applications.

The spring force of the bent wire presses onto the elastic hose material to provide a tight connection. The wire spring clamp is installed by pressing the two arms together with a pliers to open the clamp.

see also...

ganternorm.com

DIN 3016 Loose Clamps (Steel, with Elastomer Insert)

DIN 3017 Hose Clamps (Steel / Stainless Steel)

DIN 3017 T-Bolt Hose Clamps (Steel / Stainless Steel)

How to order

GN3017.5-12,8-ST

1 d₁

2 Material