



3 Type

- A** With threaded stud
- B** With internal thread

1 d_1	2 d_2	d_3	l_1	$l_2 \pm 1$	$l_3 \pm 1$	A/F	t min.
25	M 6	10	11	37,5	15	8	10
32	M 8	13	13	48	19	10	12
40	M 10	16	14	61	24	14	16
50	M 12	20	21	78	31	17	16

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 110 °C
- Black, shiny finish
- Spindle
Stainless Steel AISI 303
Matte shot-blasted
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- With inch threads

Information

Revolving ball knobs GN 319.5 are in general used where a „pulling action“ is involved such as on vertically positioned handwheels.

see also...

- *Revolving Softline Mushroom Shaped Handles GN 597.1* → Page 45

How to order

GN319.5-25-M6-B

1	d_1
2	d_2
3	Type

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

