



1		2		3							
b	d		$l_1 \pm 0,5$	a	h	l_2	l_3	l_4	$t_{min.}$		
36	M 6	M 8	200	24	57	236	164	290	15		
36	M 6	M 8	250	24	57	286	214	340	15		
36	M 6	M 8	300	24	57	336	264	390	15		
36	M 6	M 8	400	24	57	436	364	490	15		
36	M 6	M 8	500	24	57	536	464	590	15		
36	M 6	M 8	600	24	57	636	564	690	15		

Specification

Handle tube

Aluminum

- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
- Anodized, natural color ● **ELS**
- Anodized, natural color ● **ELG**
- Handle legs / Covers, black, matte finish
- Handle legs / Covers, light gray, matte finish

Handle legs / Covers

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature up to 100 °C

Bushing

Steel, zinc plated

RoHS

Characteristic for the design of the GN 366 oval handles: Tube and handle leg are made in the same elliptical profile.

see also...

	Page
GN 334 Oval Tubular Handles (Mounting from the Back)	QVX

Technical Information

Load Rating Information	QVX
Plastic Characteristics	QVX

How to order

1	b
2	d
3	l_1
4	Finish

GN 366-36-M8-400-ELS