



Inox
Stainless
Steel

3 Type

- N** Without indicator point
- M** With indicator point

1 d_1	2 d_2 H8		d_3	h	Length l	t min.
24	B 5	B 6	M 4	16	4	10
28	B 6	B 8	M 4	18	4	11

Specification

Knob

- Stainless steel AISI 304
- Matte shot-blasted finish
- Indicator point for type M
- Laser-engraved

MT

Grub screw DIN 916

- Stainless steel
- with internal hex and serrated point

RoHS

see also...

GN 436.1 Control Knobs (with Scale Lug) **Page**
QVX

Technical Information

ISO Fundamental Tolerances QVX

How to order

GN 436-24-B6-N-MT

- 1** d_1
- 2** d_2
- 3** Type
- 4** Finish

