





**elesa**  
Original design THR.

**Identification no.**  
1 Without vent hole



| <b>1</b> <b>d<sub>1</sub></b> | <b>2</b> <b>d<sub>2</sub></b> | <b>l<sub>1</sub></b> | <b>l<sub>2</sub></b> | <b>s</b> |
|-------------------------------|-------------------------------|----------------------|----------------------|----------|
| 32                            | G 1/2                         | 29                   | 11                   | 4        |
| 37                            | G 3/4                         | 32,5                 | 12                   | 5        |
| 44                            | G 1                           | 36                   | 13                   | 6        |

**Specification**

**Threaded plug**

Plastic, polyamide (PA)  
Black, matte finish

**O-Ring**

Acrylonitrile butadiene rubber (NBR)

**Operating temperature** -30 °C to +100 °C

RoHS

Threaded plugs GN 443 with the external diameter  $d_1$  match the screw-in holes for DIN 3852 pipe fittings.  
The O-ring is embedded in a radial groove on the flat side. This protects against loss and prevents it from being squeezed out during tightening.

see also... [ganternorm.com](https://ganternorm.com)  
**GN 741 | GN 742** Threaded Plugs (with External Hex)  
**GN 745 | GN 745.2** Threaded Plugs (with Seal / with O-ring)  
**GN 441 | GN 442** Threaded Plugs (Aluminum)  
**GN 443.13** Threaded Plugs (Plastic, with Loss Protection)  
**GN 548.1** Plugs (Plastic)

**Technical Information**

Plastic Characteristics

**Accessory**

**GN 7490** Welding Sockets (Steel / Stainless Steel)

| How to order            | 1 <b>d<sub>1</sub></b>      |
|-------------------------|-----------------------------|
|                         | 2 <b>d<sub>2</sub></b>      |
|                         | 3 <b>Identification no.</b> |
|                         | 4 <b>Color</b>              |
| <b>GN 443-44-G1-1-B</b> |                             |