




Original design M.243



Length l	a	b	d	h	t min.
86 ±0,5	17	26	M 6	43	12
117 ±0,5	20	30	M 8	54	13
179 ±1,0	20	30	M 8	62	13

Specification

Handle

Plastic, Phenolic Resin (PF)

- Operating temperature -30 °C bis +120 °C
- Black, shiny finish
- Flash mark cleaned and polished

Threaded bushing

Brass

RoHS

Cabinet U-handles GN 525 are known for their good design and the well proven elliptical profile. They meet the demand from an ergonomical angle.

see also...

GN 565 Cabinet U-Handles (Aluminum)

Page

QVX

Technical Information

Strength Properties

QVX

Plastic Characteristics

QVX

How to order


GN 525-117

1 Length l