



1 d ₁	2 d ₂	3 Length l	d ₄	h ₁	h ₂
45	M 6	20	19	25	22,5
45	M 8	25	19	25	22,5
63	M 8	25	26	28	25
80	M 10	30	32	36	30
100	M 12	40	36	42	36

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 130 °C
- Black, matte finish
- Threaded stud
Steel
Zinc plated, blue passivated
- *Plastic Characteristics* → Page 2158
- **RoHS**

Information

Three-lobed knob screws GN 5330 have been developed for heavy duty applications. Due to its shape, higher torque can be achieved.

How to order

GN 5330-100-M12-40

1	d ₁
2	d ₂
3	Length l

