



**4 Type**

**E** With cover cap  
(threaded blind bore)

**5 Loss protection**

**P** With plastic ball chain

**1** **2** **3**

d <sub>1</sub>	d <sub>2</sub>	Length l				d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	r	t
25	M 5	10	16	20	25	13	19	8	2,75	20	10
32	M 6	16	20	25	30	15	23	10	2,75	21	12
40	M 8	20	25	30	40	17	27	12	2,75	21,5	18
50	M 10	20	25	30	40	19	32	14	2,75	22,5	20
63	M 12	30	40	50	-	22	37	16	2,75	24	26

**Specification**

- Plastic  
Technopolymer (Polypropylen PP)  
- Reinforced, shock resistant  
- Temperature resistant up to 60 °C  
- Black, matte finish
- Threaded bushing  
Brass
- Threaded stud  
Steel zinc plated, blue passivated
- Retaining ring / ball chain  
Technopolymer (Polyacetal POM)
- Key ring  
Stainless steel, blackened
- *Plastic Characteristics* → Page 2158
- RoHS

**On request**

- Plastic ball chains with other lengths

**Information**

Star knobs with threaded stud GN 5337.13 can be captively attached to a base element with the help of a ball chain.

The star knobs are supplied ready **assembled** (with a plastic ball chain).

see also...

- *Star Knobs GN 6336.13 (with Loss Protection)* → Page 551
- *Star Knobs GN 5337.2 (with Threaded Bushing)* → Page 560
- *Star Knobs GN 5337.2 (with Threaded Stud)* → Page 561
- *More Star Knobs with Loss Protection GN 111.7* → Page 2084

How to order (Threaded bushing)

- |          |                 |
|----------|-----------------|
| <b>1</b> | d <sub>1</sub>  |
| <b>2</b> | d <sub>2</sub>  |
| <b>4</b> | Type            |
| <b>5</b> | Loss protection |

**GN 5337.13-40-M8-E-P**

How to order (Threaded stud)

- |          |                 |
|----------|-----------------|
| <b>1</b> | d <sub>1</sub>  |
| <b>2</b> | d <sub>2</sub>  |
| <b>3</b> | Length l        |
| <b>5</b> | Loss protection |

**GN 5337.13-50-M10-30-P**