



elesa
Original design VCT-SST.p



Inox
Stainless
Steel

1

2

3

d ₁	d ₂	Length l				d ₃	d ₄	h ₁	h ₂ ≈
25	M 5	10	16	20	25	13	8	19	8
32	M 6	16	20	25	30	15	10	23	10
40	M 8	20	25	30	40	17	13	27	12
50	M 10	20	30	40	45	19	15	32	14
63	M 12	30	40	50	-	22	19	37	16
74	M 12	30	50	-	-	26	17	43,5	22
84	M 16	30	50	70	-	28	17	44	21

Specification

- Plastic
Technopolymer (Polypropylene PP)
 - Reinforced, shock resistant
 - Temperature resistant up to 90 °C
 - Black, matte finish
- Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Cover caps in other colors
(standard color: black)

Information

see also...

- *Star Knobs GN 5337.2 (Threaded Stud, Steel)* → Page 561
- *Star Knobs with Threaded Stud GN 5337.4 (Threaded Stud, Stainless Steel)* → Page 565
- *Softline Star Knobs GN 5337.6 (Threaded Stud)* → Page 566
- *Star Knobs GN 5337.7 with Loss Protection GN 111.7* → Page 2084

How to order

GN 5337.7-40-M8-25

1	d ₁
2	d ₂
3	Length l