



4 Type

- A** With reflector
- B** Without reflector

2

3

d₁ Viewing window	d₂ H11 Bore Ø	d₃	b min.	l₁	l₂
9	17	18	5	7	3
12	20	21	6	7	3
17	26	28	6	7	3
20	30	32	7	8	4
25	35	38	8	9	4
28	40	43	9	10	4
32	45	47	9	11	5

Specification

- Body
Plastic
Crystal clear Polycarbonat (PC)
 - High mechanical strength
 - Temperature resistant up to 100 °C
 - Not solvent resistant
 - Not alcohol resistant
- O-ring
Rubber NBR (Perbunan®)
- Reflector
Aluminum
 - White lacquered
 - With red mark for oil level

- *ISO Fundamental Tolerances* → Page 2151
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158

• RoHS

1

NO

Information

This oil sight glass GN 542 do not require a thread.
The window glass is recessed, giving better protection to the window.

Assembly instruction:

Press in the oil sight glass manually, then possibly use an intermediate layer such as wood or a hammer. Chamfer hole 1x45° and grease slightly the outside surface of the O-ring to make assembly easier.

see also...

- *Oil Sight Glasses GN 537 (without Thread)* → Page 1560

How to order

GN 542-NO-17-26-A

1	Material
2	d₁
3	d₂
4	Type