



$d_1$		$d_2$	Length l	t
G 1	-	42	16	11
G 2	M 60 x 2	70	26	18

## Specification

- Plastic (Polyamide PA)
  - Temperature resistant up to 100 °C
  - Black, matte finish
- Seal
  - Rubber NBR (Perbunan®)
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

How to order

**GN 548.2-G1**

1  $d_1$