



b	Length l						a	d	h	r	t min.
	100	112	117	120*	-	-					
20	100	112	117	120*	-	-	13	M 6	49	13	10
20	128	160	180*	200	235*	-	13	M 6	51	13	10
26	112	117	120	125	128	-	17	M 8	55	17	12
26	160	179	192	300	400	500	17	M 8	57	17	12

* suitable for 19" rack and enclosure layout

Specification

Aluminum

- Powder coated, textured finish
 - Black, RAL 9005, UV-resistant
 - Red, RAL 3000
 - Silver, RAL 9006
- Powder coated, antimicrobial
 - Black, RAL 9005
 - White, RAL 9016
- Anodized, natural color
- Plain finish, tumbled

- **SW**
- **RS**
- **SR**
- **SMA**
- **WSA**
- **EL**
- **BL**

RoHS

Cabinet U-handles GN 565 are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

In addition to the standard surfaces, these cabinet U-handles are also available with a functional coating.

The **SW** version is coated with a highly weather-resistant and UV-resistant powder coating system, making this version excellent for outdoor use.

The **SMA / WSA** versions have a powder coating based on silver ions, which gives them antimicrobial properties. The principle of action has been shown to reduce the contamination of the handle surfaces within 24 hours so that fewer than 1% of bacteria and fewer than 5% of viruses ultimately survive.

Standard parts with antimicrobial powder coating are primarily used in the health care sector and in public buildings, such as airports, train stations, stadiums, etc.

see also...	Page
GN 565.1 Cabinet U-Handles (Aluminum, Mounting from the Operator's Side)	QVX
GN 565.2 Inclined Cabinet U-handles (Aluminum, Mounting from the Back or the Operator's Side)	QVX
GN 565.5 Cabinet U-Handles (Stainless Steel, Mounting from the Back or the Operator's Side)	QVX

Technical Information

Load Rating Information	QVX
-------------------------	-----

Accessory

GN 181 Fastening Sets (Mounting from the Operator's Side)	QVX
--	-----

<p>How to order</p> <p>GN 565-20-100-SW</p>	1	b
	2	Length l
	3	Finish