



elesa
Original design BT-p-SST

ROSTFREI
Inox
Stainless
Steel

d₁	d₂	Length l					d₃	h	k
12	M 3	6	10	16	-	-	9,5	11,5	7,5
16	M 3	6	10	16	-	-	11	13	8
16	M 4	6	10	16	-	-	11	13	8
16	M 5	10	16	25	-	-	11	13	8
20	M 5	10	16	25	-	-	12	16	10
20	M 6	10	16	20	25	30	12	16	10
25	M 6	16	20	25	30	-	16	19	11
32	M 8	16	20	30	-	-	17	22	13

Specification

Knob

Plastic, Polyamide (PA)

- Reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

Threaded stud

Stainless steel AISI 303

RoHS

Knurled nuts GN 591.5 are used for quick, tool-free mounting or adjusting of fixtures and devices.

With the stainless steel threaded studs, they are also suitable for applications that place increased demands on the corrosion resistance of the components used.

see also...

	Page
GN 591 Knurled Screws (Threaded Stud Steel)	QVX
GN 421 Knurled Screws	QVX

Technical Information

Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order

GN 591.5-20-M5-16

1	d ₁
2	d ₂
3	Length l