



elesa  
Original design M.943

<sup>1</sup> l <sub>1</sub> ±0,5	<sup>2</sup> d <sub>1</sub> Thread	<sup>2</sup> d <sub>2</sub> Bore	b	h	l <sub>2</sub>	l <sub>3</sub>	s	t min.
88	M 5	B 4,5	13,5	36,5	112	74,5	9	10
120	M 5	B 4,5	15	42	144	106,5	11	10

**Specification**

**Handle**

- Plastic, Polyamid (PA)
- Glass fiber reinforced
- Operating temperature -30 °C to +130 °C
- Black, matte finish

**Bushings**

Brass

RoHS

The dimensions of the cabinet U-handles GN 627 match 19" inserts.

Cabinet U-handles GN 627 have been designed for fixing with sheet-metal screws with thread size ST 4.8, such as fillister-head screws DIN ISO 7049. The maximum recommended tightening torque is 5 Nm.

see also...

	Page
GN 427 Cabinet U-Handles (Aluminum, Ellipse Shaped Profile)	QVX
GN 427.5 Cabinet U-Handles (Ellipse Shaped Profile)	QVX
GN 425 Cabinet U-Handles (Aluminum / Stainless Steel)	QVX

**Technical Information**

Strength Properties	QVX
Plastic Characteristics	QVX

How to order

**GN 627-88-M5**

<sup>1</sup> l <sub>1</sub>
<sup>2</sup> d <sub>1</sub> (d <sub>2</sub> )