



1.1

1.2

1.3

1.4

2

3

4

d ₁	d ₂	Length l				d ₃	h ₁	h ₂	
40	M 8	20	25	30	40	-	14	25	13
50	M 10	20	25	30	45	55	18	32	18
63	M 12	30	40	50	-	-	20	40	23

2.1

Specification

- Knob
Stainless steel
precision casting AISI 316
Polished
- Threaded stud
Stainless steel
- The threaded stud is screwed in and secured by a cross-dowel.
- *Stainless Steel Characteristics* → Page 2166
- RoHS

1
A4P

Information

Hand knobs GN 6335.5 satisfy the dimensions of the DIN 6335 Type L but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygiene requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- *Hand Knobs GN 6335.4 / GN 6336.5 (Plastic)* → Page 587
- *Hand Knobs GN 6335.4 / GN 6336.5 (Cast Iron / Stainless Steel / Aluminum)* → Page 583
- *Star Knobs with Threaded Stud GN 5334 / GN 5334.4 (Stainless Steel)* → Page 575

2.2

2.3

2.4

How to order	1	Material
	2	d ₁
GN 6335.5-A4P-40-M8-25	3	d ₂
	4	Length l

