



1.1

1.2

1.3

1.4

2

3

4

d <sub>1</sub>	d <sub>2</sub>	Length l					d <sub>3</sub>	h <sub>1</sub>	h <sub>2</sub>
40	M 8	20	25	30	40	-	14	25	12
50	M 10	20	25	30	45	55	18	32	15
63	M 12	30	40	50	-	-	20	40	19

2.1

**Specification**

- Knob  
Stainless steel  
precision casting AISI 316  
Polished
- Threaded stud  
Stainless steel A4
- The threaded stud is screwed in and secured by a cross-dowel (stainless steel).
- *Stainless Steel Characteristics* → Page 2166
- RoHS

1

A4P

**Information**

Stainless steel star knobs GN 6336.5 satisfy the dimensions of the DIN 6336 Type L but differ in terms of their non-scooping geometry, which makes cleaning easier and helps prevent possible build-up of dirt.

They are suitable for areas with special hygiene requirements and, thanks to the material used, for applications in highly corrosive environments.

see also...

- *Star Knobs GN 6336.4 / GN 6336.5 (Plastic)* → Page 545
- *Star Knobs GN 6336.4 / GN 6336.5 (Cast Iron / Stainless Steel / Aluminum)* → Page 541
- *Star Knobs with Threaded Stud GN 5334 / GN 5334.4 (Stainless Steel)* → Page 575

2.2

2.3

2.4

How to order		1	Material
	1	2	d <sub>1</sub>
	2	3	d <sub>2</sub>
	3	4	Length l
<b>GN 6336.5-A4P-63-M12-40</b>			

