




1	2	d ₁		b	d ₃	h ₁	h ₂	h ₃	h ₄	r
		Brass	Stainless steel							
48	M 5	M 6	-	7	13,5	24	5,5	12	22	20,5
55	M 6	M 8	M 8	8	16	28	6,5	18	25	21,5
63	M 8	M 10	M 10	9	19	32	7,5	20	29	22,5

Specification

Knob

Plastic, polyamide (PA)

• Glass fiber reinforced

• Black-gray, matte finish similar to RAL 7021

Threaded bushing

• Brass

• Stainless steel AISI 303

M

N

Cover cap

Plastic, polyamide (PA)

Black-gray, RAL 7021, matte finish

Retaining ring / Ball chain

Plastic, polyacetal (POM)

Black

Key ring on type P

Stainless steel AISI 301

chemically blackened

Operating temperature

0 °C to +60 °C

RoHS

Accessory

ganternorm.com

GN 111.3 Key Rings (Stainless Steel)

GN 111 Ball Chains (Brass)

GN 111.5 Ball Chains (Stainless Steel)

GN 111.2 Retaining Cables (Stainless Steel)

GN 111.8 Retaining Cables (Stainless Steel Quality Class 4)

GN 111.4 Spiral Retaining Cables (Plastic)

4

Type

R With retaining ring

P With plastic ball chain

How to order

1

2

3

4

GN 634.13-48-M6-M-R

1

d₁

2

d₂

3

Material

4

Type

2.2 Tensioning, Clamping with Knobs

1