



3 Type

- A Without knurl
- B With knurl

1

2

d ₁	d ₂	d ₃	h ₁	h ₂	t min.
21	M 4	12,5	18	10,5	10
21	M 5	12,5	18	10,5	10
25	M 6	14,5	22,5	14	12
25	M 8	14,5	22,5	14	12
31	M 8	18,5	27	17	15
31	M 10	18,5	27	17	17

Specification

GN 676.1

Steel
blackened

GN 676.2

Steel
Zinc plated, blue passivated

GN 676.5

Stainless Steel AISI 303
Matt shot-blasted

RoHS

Knobs GN 676.1 / GN 676.2 / GN 676.5 are used in applications where a push or pull movement is required. Their concave top gives a more comfortable thumb grip.

The version with knurl (type B) can be used as a knurled nut.

see also...

	Page
GN 676 Knurled Knobs (Plastic)	QVX
GN 676 Knurled Knobs (Detectable Plastics)	QVX
GN 676 Knurled Knobs (Antibacterial Plastic)	QVX
GN 75 Mushroom Shaped Knobs (Steel)	QVX
GN 75.5 Mushroom Shaped Knobs (Stainless Steel)	QVX

Technical Information

Stainless Steel Characteristics QVX

How to order (Steel, blackened)

1	d ₁
2	d ₂
3	Type

GN 676.1-21-M5-B

How to order (Steel, zinc plated)

1	d ₁
2	d ₂
3	Type

GN 676.2-25-M6-B

How to order (Stainless steel)

1	d ₁
2	d ₂
3	Type

GN 676.5-31-M10-A