


ROSTFREI
Inox
Stainless
Steel

d₁	d₂ H10		b₁	b₂	d₃	s	x ≈ Max. protrusion of cap screw	Adjustable hand lever for d ₃ 
30	B 12	-	11	13	M 4	2,1	0,7	GN 311-30-M4-12-SW
32	B 14	-	11	13	M 4	2,1	0,7	GN 311-30-M4-12-SW
36	B 15	B 16	13	15	M 5	2,1	1,4	GN 311-30-M5-13-SW
42	B 18	B 20	15	18	M 5	3	0,6	GN 311-30-M5-15-SW
48	B 22	B 25	15	18	M 5	3	0	GN 311-45-M5-16-SW
55	B 28	B 30	15	18	M 6	3	0,5	GN 311-45-M6-18-SW
60	B 32	B 35	15	18	M 6	4	0,4	GN 311-45-M6-19-SW
65	B 40	-	15	18	M 6	4	0,5	GN 311-45-M6-20-SW

Specification

- Stainless steel AISI 316LHC Sintered **NI**
- Damping washer Elastomer (PUR) - 70 Shore A - Temperature resistant up to 80 °C - Transparent
- Socket cap screw DIN 912 Stainless steel AISI 304
- ISO Fundamental Tolerances → Page 2151
- Elastomer Characteristics → Page 2158
- Stainless Steel Characteristics → Page 2166
- RoHS

Information

The affixed damping washer of the semi-split shaft collars GN 7062.3 absorbs mild shocks and has a sound-damping effect when the shaft collars come into contact with other components.

They can be assembled safely and easily with a high clamping force by reducing the slot height, without damaging the surface of shafts and axles.

The thread d₃ for sizes d₁ = 30 to 36 is designed as a through hole; for sizes d₁ = 42 and larger, it is designed as blind hole.

see also...

- Split Shaft Collars GN 7072.3 (with Damping Washer) → Page 1157
- Semi-Split Shaft Collars GN 706.2 → Page 1148

Accessory

- Adjustable Hand Levers GN 311 → Page 1159

How to order

GN 7062.3-42-B18-NI

1	d ₁
2	d ₂
3	Material

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

