





Reference arrow



3 Type

- A With friction ring
- B Without friction ring

¹ d ₀ Control knob Ø GN 723.4	² d ₁	d ₂ H8		d ₃ -0,1	d ₄	k	l ₁	l ₂
27	33,5	B 6	-	23,3	3,4	13	11,2	4
34	41	B 6	B 8	29,3	3,4	18	14,2	5
42	50	B 8	B 10	37,3	4,5	24	16,2	5

Specification

Flange

- Aluminum
- Anodized, black
- Reference arrow
- White
- Laser-engraved

Clamp ring

Rubber

Friction ring

Plastic, polyamide (PA)

RoHS

Reference flanges GN 723.3 are used together with control knobs GN 723.4 which offer the following advantages:

- they have a reference mark to line up with the control knob scale,
- they offer additional support for the control shaft,
- the version with friction ring prevents an unexpected movement of the control knob by vibration.

see also...

GN 723.4 Control Knobs (Aluminum) Page QVX

Technical Information

ISO Fundamental Tolerances QVX

Plastic Characteristics QVX

How to order

GN 723.3-50-B8-A

¹	d ₁
²	d ₂
³	Type

