

**3 Type**

- O Neutral
- E With DIN fill symbol
- A With DIN drain symbol

4 Identification no.

- 1 Without vent drilling

1

2

d ₁	d ₂	d ₃	e ≈	l ₁	l ₂	s	t
19	G 1/4	M 14 x 1,5	M 5	17,3	15,5	8	15
22	G 3/8	M 16 x 1,5	M 5	20,8	15,5	8	18
26	G 1/2	M 20 x 1,5	M 5	24,3	16	8,5	21
32	G 3/4	M 26 x 1,5	M 5	31,2	17	9	27
40	G 1	M 33 x 1,5	M 5	37	19,5	11	32

Specification

- Stainless steel AISI 316L
Plain finish, tumbled
- Seal
Fluoro-elastomer (FPM / FKM)
 - Brown
 - Temperature resistant up to 180 °C
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

On request

- Other thread sizes
- With dipstick
- With acrylonitrile butadiene rubber (NBR) seal GN 741.5

Information

Threaded plugs GN 742.5 can be used in particularly aggressive environments thanks to the material used.

The seal is embedded in a radial recess and thus cannot be lost, squeezed out or overloaded during tightening.

The outer diameter d₁ of the stainless steel threaded plugs GN 742.5 is matched to screw-in holes for pipe fittings according to DIN 3852.

see also...

- *Threaded Plugs GN 741 / GN 742 (Aluminum)* → Page 1590
- *Threaded Plugs GN 749 (Steel, Zinc Plated)* → Page 1592
- *Threaded Plugs GN 740 / GN 747 (Plastic)* → Page 1586 / 1587
- *Threaded Plugs GN 442 (Aluminum, with Wing Knob)* → Page 1592

How to order

1	d ₁
2	d ₂
3	Type
4	Identification no.

GN 742.5-40-M33X1,5-A-1

