



elesa  
Original design TPC.

### 3 Type

- A Without dipstick
- B With dipstick

### 4 Identification no.

- 1 Without vent hole
- 2 With vent hole

1

2

d <sub>1</sub>	d <sub>2</sub> +0,2	d <sub>3</sub> Vent hole	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	l <sub>4</sub>	l <sub>5</sub>
30	20	2	14	29	6,5	10,5	188
35	26	2	14	29	6,5	10,5	188

## Specification

- Plastic (Polypropylene PP)
  - Temperature resistant up to 100 °C
  - Black, matte finish
- O-rings  
Rubber NBR (Perbunan®)
- Dipstick  
Steel, phosphated
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

## On request

- Level Markings / Special Lengths GN 109  
→ Page 2083

## Information

Oil filler plugs GN 748 with DIN „fill“ symbol do not require a thread. They are for push-fit and the minimum wall thickness of the tank must be 6,5 mm (l<sub>3</sub>).

MAX-MIN lines can easily be marked on the two flat sides of the dipstick (see GN 109 → Page 2083).

### How to order

GN 748-30-20-B-1

1	d <sub>1</sub>
2	d <sub>2</sub>
3	Type
4	Identification no.