



2 Type

- E** For single joints
- D** For double joints

1

d ₁ Joint-Ø	d ₂ Type E	d ₃ Type E	d ₄ Type D	d ₅ Type D	l ₁ Type E	l ₂ Type D
16	15	28	16	35	34	55
22	20,5	40	20	36	45	65
25	24,5	48	24	44	50	70
28	27,5	52	28	51	56	80
32	30,5	56	32	62	65	90
36	35,5	66	-	-	72	-
42	40	75	40	73	82	120
45	45	84	-	-	95	-
50	50	92	50	90	108	155
58	56	100	-	-	122	-

Specification

- Type E
Rubber (CR)
Black
- Type D
Elastomer plastic
Smooth PVC
Black
- *Elastomer Characteristics* → Page 2158
- *Plastic Characteristics* → Page 2158
- RoHS

2

Information

- E** Gaiters GN 808.1 give universal joints full protection against ingress of dirt.
 - D** At the same time they can be filled with grease which gives long term lubrication for universal joints with friction bearing.
- The gaiters are secured at each end with two cable ties, which are supplied each sleeve.

How to order

GN808.1-25-E

1 d₁

2 Type

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9

