



¹ d ₁	² d ₂	b	d ₃	h ₁	h ₂ ≈	t min.
32	M 5	4	9	18	3	8
32	M 6	4	9	18	3	9
40	M 6	4	11	21	3	9
40	M 8	4	11	21	3	12
50	M 8	6	13	26	3	12
50	M 10	6	13	26	3	15
63	M 10	11	16	33	4	15
63	M 12	11	16	33	4	18

Specification

Stainless steel precision casting AISI 316

- Matte shot-blasted finish
- Polished



MT
PL

RoHS

Wing nuts GN 8340 clamp and fasten parts easily without tools. The ergonomic shape allows for high tightening forces.

The wing nuts can also be used in particularly aggressive environments thanks to the material used.

see also...

	Page
GN 8341 Wing Nuts (Hygienic Design)	QVX
GN 8350 Wing Screws	QVX
GN 432 Wing Nuts	QVX
GN 434 Wing Nuts	QVX
GN 834 Wing Nuts	QVX
GN 5063 T-Handles	QVX

Technical Information

Stainless Steel Characteristics

QVX

How to order

GN 8340-¹32-²M5-³MT

1	d ₁
2	d ₂
3	Finish