



elisa
Original design BAG2-120

ROSTFREI
Inox
Stainless
Steel

1 d ₁ Bore	2 d ₂ Bore		For tube outside Ø	Standard description in inch
B 42,4	B 42,4	-	42,4	1 1/4"
B 48,3	B 42,4	B 48,3	48,3	1 1/2"
B 60,3	B 42,4	B 48,3	60,3	2"

Specification

- Plastic (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 100 °C
 - Black, matte finish
- Hexagon screws DIN 931
Stainless steel AISI 304
- Hexagon nuts DIN 934
Stainless steel AISI 304
- Washers
Stainless steel AISI 304
- *Plastic Characteristics* → Page 2158
- *Stainless Steel Characteristics* → Page 2166
- RoHS

Information

- see also...**
- *Base Plate Connector Clamps GN 85 (Plastic)* → Page 1814
 - *Leveling Feet* → Page 1424 ff.
 - *Construction Tubes GN 990* → Page 1835

How to order	1	d ₁
GN 84-B60,3-B42,4	2	d ₂